



videofied™
Made by RSI VIDEO TECHNOLOGIES

Indoor MotionViewer™
DCV

INSTALLATION DATA SHEET


Made by RSI VIDEO TECHNOLOGIES



Installation height of the pet immune camera :
2m10 (6 1/2') to the bottom of the camera



The detector must be fixed with a screw, one of which must be positioned in the tear-off zone



	Pet immune	Installation height
DCV200 DCV600 DCV700	NONE	From 2m10 (6 1/2') to 2m30 (7 1/2') to the bottom of the camera
DCVA200 DCVA600 DCVA700	YES 18 KG (40lbs)	Must imperatively be 2m10 (6 1/2') to the bottom of the camera

Recording of the detector

The alarm panel must be placed in "Recording device", mode then and the keypad must display **"PRESS PROGRAM BUTTON OF DEVICE"**.

- 1 Insert the 3 Lithium batteries **LS14500** (in the same direction).
- 2 Press the PROGRAM BUTTON of the detector, release as soon as the indicator flashes.
- 3 With the aid of the keypad, continue recording by running the Radio Range Test and allocating an area....

Always place the camera on an unobstructed angle.

- > Possibility of testing the RF range.
- > Possibility of testing the detection cover range.

* This indicator will no longer flash from then on except at opening or during a detection test.

DCV means DCV600 for USA/Canada, DCV700 for Australia/Singapore and DCV200 for Europe and rest of the world.



videofied™
Made by RSI VIDEO TECHNOLOGIES

EMEA SALES

2, rue Alexis de Tocqueville
92160 ANTONY
FRANCE
Hot line : +33 (0)820 846 620 / UK : 0871 951
Fax : +33 (0)3 90 20 66 36

North American Headquarter

4455 White Bear Parkway, Suite 700
White Bear Lake, MN 55110
USA
Hot line : 877-206-5800
Fax : 651-762-4693

www.videofied.com

